Plan View

ÂERO


Using Your Setup Instructions

The Aero Overhead Sign Setup Instructions are created specifically for your configuration. They include an exploded view of the frame which is sequentially numbered. We encourage you to study the instructions before attempting to assemble your exhibit.


Connections are kept very simple: no tools. Everything assembles with push-button connectors and pre-connected horizontal sections.


Cleaning and Packing Your Display

- 1) Use care when cleaning aluminum extrusion or acrylic inserts. Use only non-abrasive cleaners.
- 2) Retain all packing material. It will make re-packing much easier and will reduce the likelihood of shipping damage.



Connections are made by holding the button down and sliding the red tube into opposing tube until the connection is made. To disassemble push button and pull or twist extrusions apart.






NOTE:

PDF copies of your Setup Instructions are available @ www.classicexhibits.com Use the Search Tool located on the lower left-hand corner of the Classic Home Enter your 5-7 digit Order #. Search for Setup Instructions

866.652.2100



Harness Strength Calculation

Hanging sign weight is calculated based on weight of the structure and the weight of the fabric:

- The weight of the structure material is 0.29 lbs per linear feet
 The weight of the fabric is 0.04 lbs per sq. feet

Based on information above, one string of the harness at a standard 45 degree sling angle will accommodate 163 sq. feet surface measured sign. The vertical string will hold 233 sq. feet surface measured sign.

NOTE: If motor used for rotation, see motor specification.

Construction consists of the following materials:

- 1. 302/304 (1/8") Stainless Steel Cable (Rated at 1760 lbs break strength)
- 2. Plated Spring-loaded Interlocking Snaps (Rated at 280 lbs working load)
- 3. Nicoperss Oval Sleeves (Holding strength rated at 900 lbs)
- 4. 0.25" x 4" Diameter T6061 Aluminum Plate
- 5. Eye Bolts (Rated 900 lbs on vertical lift and 450 lbs on 45 degree lift)

Detail A			Detail B 10c					
	Harness Head Assembly			Harness Tail Assembly				
MK	Qty	Desc		MK	Qty	Desc		
10e	1	.313 Nylok Hex Nut		10c	2.7	125 Copper S	top 520)-20040
100		.515 Nylok Hex Nut		10f	<u>-</u>	.125 Copper S .313 Kidney S	nan 434	-24905
				101		is is idiality s	רכד קטוו	27703
						Typical 4 Plac	- <u>C</u> C	
I	1					i iypicai 4 Flac	.८১	